


## LMC-40



### **DEVICE**

### 40 GHz Lightwave Modulator with Bias Control

OVERVIEW

The Optilab LMC-40 is a high-performance Lightwave Modulator Board designed for analog photonics applications from 10 MHz to 40 GHz. This unit includes a 30 GHz optical intensity modulator and an Automatic Bias Control (ABC) board with four different operating modes. The external laser source can be any polarization maintaining device, such as a tunable laser or narrow linewidth laser, making it a versatile solution for OEM-based system integration. Contact Optilab for more information.

### **FEATURES**


- Automatic Bias Control w/ 4 mode operation
- Accepts external laser source via input
- Customizable Options:
  - Low Drive Voltage
  - PM output
  - High Extinction Ratio (> 30 dB)
  - Temp. Qualified (-55°C to +75°C)

### **USE IN**


- Picosecond pulse generation
- Optical communications to 43 Gb/s
- Active mode lock (PM version)

- Analog photonics
- 40 GHz RFoF transmission
- RF/IF signal distribution
- Satellite communication

### **FUNCTIONAL DIAGRAM**







# LMC-40

### **SPECIFICATIONS**

1520 nm to 1610 nm Operating Wavelength Laser Source User's external input Optical Input Level +20 dBm max. >15 dB @ 10 GHz; >10 dB @ 30 GHz RF Return Loss 10 MHz to 40 GHz Operating Frequency Range Input RF Voltage 27 dBm max. 6.5 dBm typ. w/ 20 mW DFB Optical Output Level 3 dB, 28 GHz typ. S21 Bandwidth 4 Automatic bias control modes, selectable by software Modulator Bias Mode 25 dB typ., >30 dB (HE version) **Extinction Ratio**  $2.5\,V$  typ.  $\, \blacksquare$  10 GHz,  $4.3\,V$  typ.  $\, \blacksquare$  30 GHz Modulator Voltage

**GENERAL** 


### MECHANICAL

Operating Temperature (standard)	-30 °C to +60 °C
Operating Temperature (TQ version)	-55 °C to +75 °C
Storage Temperature	-60 °C to +90 °C
Power Supply Requirements	± 5 V DC, 1 A max.
Optical Connector	FC/APC
Fiber Type	PANDA input, SMF-28 output; PANDA input/output (PM version)
RF Input Connector	2.92mm Female
Power Connector	4 Pin Molex
Remote Control	USB 2.0 software included
Alarm	LED bias mode status
Dimensions	241 mm x 152 mm x 41 mm


BIAS CONTROL MODE


Mode	Operation Conditions
<u>[]</u> +	Set to quadrature point of positive slope for linear analog modulation
Q-	Set to quadrature point of negative slope for linear analog modulation
Min.	Set to min. point of operation for pulse generation or digital modulation
Мах.	Set to max. point of operation for pulse generation or digital modulation






# LMC-40





### BIAS SETTING MODES FOR LMB

Based on sophisticated phase measurement of this small dither signal, LMC-40 provides four selectable operating modes: quadrature (Quad +), inverted quadrature (Quad -), minimum (Min), or maximum (Max) points.





**ORDERING OPTIONS** 

### LMC-40-XX-YY

XX PM: Polarization Maintaining HE: High Extinction Ratio

**YY** DC: DC +/- 5V Power Supply (Option 1)

AC: AC 100/240 VAC (Option 2)

Option 1 : DC +/- 5V



Option 2: 100/240 VAC

